

## Massive Dev Chart Search Results

Film	Developer	Dilution	ASA/ISO	35mm	120	Sheet	Temp	Notes
Academy 200	Rodinal	1+50	200	21			20C	
Acupan 200	Rodinal	1+49	100	7.5			20C	
Acupan 800	Rodinal	1+24	400	6			20C	
Adox CHM 125	Rodinal	1+100	64	21			20C	
Adox CHM 125	Rodinal	1+24	80	7.5			20C	
Adox CHM 125	Rodinal	1+50	100	12			20C	
Adox CHM 125	Rodinal	1+25	125	9			20C	
Adox CHM 125	Rodinal	1+50	125	15			20C	
Adox CHM 125	Rodinal	1+100	125	20			20C	[17]
Adox CHM 125	Rodinal	1+25	200	13			20C	
Adox CHM 125	Rodinal	1+50	200	20			20C	
Adox CHM 125	Rodinal	1+50	250	26			20C	
Adox CHM 400	Rodinal	1+100	160	20			20C	[17]
Adox CHM 400	Rodinal	1+50	200	10			20C	
Adox CHM 400	Rodinal	1+100	400	16			20C	
Adox CHM 400	Rodinal	23+1000	400	13.5			20C	
Adox CHM 400	Rodinal	1+50	400	7.25			24C	[1][26]
Adox CHM 400	Rodinal	1+50	400	11			20C	
Adox CHM 400	Rodinal	1+25	400	6			20C	
Adox CHM 400	Rodinal	1+25	800	8			20C	
Adox CHM 400	Rodinal	1+50	800	16			20C	
Adox CHM 400	Rodinal	1+25	1600	12			20C	
Adox CHM 400	Rodinal	1+50	1600	24			20C	
Adox CHM 400	Rodinal	1+25	3200	18			21C	
Adox CHS 100	Rodinal	1+50	50	9	9	9	20C	
Adox CHS 100	Rodinal	1+25	80	5			20C	
Adox CHS 100	Rodinal	1+100	100	16	16	16	20C	
Adox CHS 100	Rodinal	1+25	100	6	6	6	20C	
Adox CHS 100	Rodinal	1+50	100	10	10	10	20C	
Adox CHS 100	Rodinal	1+25	160		8		20C	
Adox CHS 100	Rodinal	1+50	200	14	14	14	20C	
Adox CHS 100	Rodinal	1+50	400	24	24	24	20C	
Adox CHS 25	Rodinal	1+100	12	9	9		20C	
Adox CHS 25	Rodinal	1+50	12	3.5			20C	
Adox CHS 25	Rodinal	1+50	20	4	4		20C	
Adox CHS 25	Rodinal	1+99	20	6.5	6.5		20C	
Adox CHS 25	Rodinal	1+100	25	17	18		21C	
Adox CHS 25	Rodinal	1+100	25	12			20C	
Adox CHS 25	Rodinal	1+25	25	4	4		20C	
Adox CHS 25	Rodinal	1+100	25	10			24C	[37][48][r]
Adox CHS 25	Rodinal	1+50	25	8	8		20C	
Adox CHS 25	Rodinal	1+100	25		11		20C	[25a]
Adox CHS 50	Rodinal	1+100	50	18	18		20C	
Adox CHS 50	Rodinal	1+25	50	6	6		20C	
Adox CHS 50	Rodinal	1+200	50			50	20C	[35a]
Adox CHS 50	Rodinal	1+50	50	9	9		20C	
Adox CMS 20	Rodinal	1+200	10	14-15			20C	[13]
Adox CMS 20	Rodinal	1+100	20	18			20C	
Adox ORT 25	Rodinal	1+25	25	4			20C	
Adox ORT 25	Rodinal	1+50	25	5			20C	
Adox ORT 25	Rodinal	1+50	25	6			20C	
Adox ORT 25	Rodinal	1+50	25	10			21C	
Adox Pan 25	Rodinal	1+50	25	11	11	11	20C	
Adox Pan 25	Rodinal	1+25	25	6	6	6	20C	
Adox Pan 25	Rodinal	1+100	25	20			20C	[25b]
Adox Silvermax	Rodinal	1+50	80	14			21	[gz]
Adox Silvermax	Rodinal	1+50	80	14			21C	[gz]
Adox Silvermax	Rodinal	1+100	100	18			21C	[dd]
Adox Silvermax	Rodinal	1+50	100	12			20C	

Adox Silvermax	Rodinal	1+25	100	8			20C	
APX 100	Rodinal	1+50	50	11.5			20C	[30]
APX 100	Rodinal	1+24	64	7.5			20C	[30]
APX 100	Rodinal	1+50	100		13		20C	[26][30]
APX 100	Rodinal	1+25	100	8	8	8	20C	
APX 100	Rodinal	1+50	100	13			20C	
APX 100	Rodinal	1+50	160	17	17	17	20C	
APX 100	Rodinal	1+50	200	21.5			20C	
APX 100	Rodinal	1+25	200	11	11	11	20C	[30]
APX 100	Rodinal	1+50	400	29			20C	
APX 25	Rodinal	1+49	12	6.5	6.5		20C	
APX 25	Rodinal	1+100	16	15	15		20C	
APX 25	Rodinal	1+100	20	20	20		20C	
APX 25	Rodinal	1+50	20-25	10	10		20C	
APX 25	Rodinal	1+25	20	6	6		20C	
APX 25	Rodinal	1+25	25	7	7		20C	
APX 25	Rodinal	1+100	25	14	14		20C	
APX 400	Rodinal	1+50	200	10			20C	
APX 400	Rodinal	1+100	200	15	15		20C	[17][30]
APX 400	Rodinal	1+24	250	5			20C	[30]
APX 400	Rodinal	1+49	250	8			20C	[30]
APX 400	Rodinal	1+50	320-500	11	11		20C	[30]
APX 400	Rodinal	1+50	320	30	30		20C	
APX 400	Rodinal	1+25	320	10	10		20C	
APX 400	Rodinal	1+25	320-400	7	7		20C	[30]
APX 400	Rodinal	1+100	400	22			24C	[a][30]
APX 400	Rodinal	1+100	400	17			24C	[a][30]
APX 400	Rodinal	1+25	800	14			20C	
Argenti LSRF	Rodinal	1+25	50	6			20C	
Argenti Protopan 400	Rodinal	1+25	400	10			20C	
Arista EDU Ultra 100	Rodinal	1+100	50	7			20C	[17]
Arista EDU Ultra 100	Rodinal	1+50	100	7			20C	
Arista EDU Ultra 100	Rodinal	1+25	100	3.5			20C	
Arista EDU Ultra 200	Rodinal	1+50	200	10			20C	
Arista EDU Ultra 200	Rodinal	1+50	200	8			20C	
Arista EDU Ultra 200	Rodinal	1+25	200	5			20C	
Arista EDU Ultra 400	Rodinal	1+25	400	5.5			20C	
Arista EDU Ultra 400	Rodinal	1+50	400	11			20C	
Arista II 100	Rodinal	1+50	50	11.5			20C	[30]
Arista II 100	Rodinal	1+24	64	7.5			20C	[30]
Arista II 100	Rodinal	1+50	100	13			20C	
Arista II 100	Rodinal	1+25	125	8			20C	
Arista II 100	Rodinal	1+50	160	17			20C	
Arista II 100	Rodinal	1+25	200	11			20C	[30]
Arista II 100	Rodinal	1+50	400	29			20C	
Arista II 400	Rodinal	1+100	200	15			20C	[17][30]
Arista II 400	Rodinal	1+50	200	10			20C	
Arista II 400	Rodinal	1+24	250	5			20C	[30]
Arista II 400	Rodinal	1+49	250	8			20C	[30]
Arista II 400	Rodinal	1+50	320	30			20C	
Arista II 400	Rodinal	1+25	320	10			20C	
Arista II 400	Rodinal	1+25	320-400	7			20C	[30]
Arista II 400	Rodinal	1+50	320-500	11			20C	[30]
Arista II 400	Rodinal	1+100	400	22			24C	[a][30]
Arista II 400	Rodinal	1+100	400	17			24C	[a][30]
Arista II 400	Rodinal	1+25	800	14			20C	
Arista Premium 100	Rodinal	1+100	64	10			20C	
Arista Premium 100	Rodinal	1+25	125	6	6	6	20C	[29]
Arista Premium 100	Rodinal	1+50	125	13	13	13	20C	[29]
Arista Premium 100	Rodinal	1+85	200	12	12	12	24C	[29]
Arista Premium 400	Rodinal	1+50	100	7.5			20C	
Arista Premium 400	Rodinal	1+50	200	9			20C	
Arista Premium 400	Rodinal	1+100	250	15			20C	[29]

Arista Premium 400	Rodinal	1+100	250	20			20C	[gz]
Arista Premium 400	Rodinal	1+24	320	6			20C	[29]
Arista Premium 400	Rodinal	1+35	400	10			20C	[29]
Arista Premium 400	Rodinal	1+100	400	20			20C	[29]
Arista Premium 400	Rodinal	1+75	400	17.5			20C	[29]
Arista Premium 400	Rodinal	1+60	400	15			20C	[29]
Arista Premium 400	Rodinal	1+50	400	13			20C	[29]
Arista Premium 400	Rodinal	1+100	400	24			21C	[m]
Arista Premium 400	Rodinal	1+25	400	7			20C	[29]
Arista Premium 400	Rodinal	1+50	640	15.5			20C	[29]
Arista Premium 400	Rodinal	1+50	800	16.5			20C	[29]
Arista Premium 400	Rodinal	1+100	800	17.5			24C	[29]
Arista Premium 400	Rodinal	1+50	1600	18.5			20C	[29]
Arista Premium 400	Rodinal	1+50	3200	33			20C	[r]
Arista Premium 400	Rodinal	1+50	3200	33			20C	[r]
Arista Premium 400	Rodinal	1+50	12800	51			20C	[35c]
Aviphot APX 200 S	Rodinal	1+25	200	7			20C	
Aviphot APX 200 S	Rodinal	1+50	200	11			20C	
Aviphot APX 200 S	Rodinal	1+25	200	5			20C	
Aviphot APX 400 S	Rodinal	1+50	200	6			24C	[37]
Aviphot APX 400 S	Rodinal	1+50	400	11			20C	
Aviphot APX 400 S	Rodinal	1+25	400	7			20C	
Aviphoto Ortho 25	Rodinal	1+99	6		5		20C	
Azopan PS-21	Rodinal	1+25	100	5			20C	
Azopan PS-24	Rodinal	1+25	200	6			20C	
BPF/BRF 100	Rodinal	1+25	100		6		20C	
BPF/BRF 100	Rodinal	1+50	100		5		20C	
BPF/BRF 15	Rodinal	1+25	15		6		20C	
BPF/BRF 15	Rodinal	1+100	15		20		20	
BPF/BRF 200	Rodinal	1+25	125-200	6.5	6.5	6.5	20C	
BPF/BRF 200	Rodinal	1+50	200	12	12	12	20C	
BW400CN	Rodinal	1+100	400	60			20C	[35a]
Classic Pan 200	Rodinal	1+50	200	10	10	10	20C	
Classic Pan 200	Rodinal	1+50	200		13		20C	
Classic Pan 400	Rodinal	1+50	400	12	12	12	20C	
Classic Pan 400	Rodinal	1+25	400	7.5	7.5	7.5	20C	
Classic Pan 400	Rodinal	1+25	800	10	10	10	20C	
Delta 100 Pro	Rodinal	1+25	50	7	7	7	20C	
Delta 100 Pro	Rodinal	1+50	50	10	10	10	20C	
Delta 100 Pro	Rodinal	1+50	100	14	14	14	20C	
Delta 100 Pro	Rodinal	1+25	100	9	9	9	20C	
Delta 100 Pro	Rodinal	1+100	100		18		20C	[33][35c][37][4]
Delta 100 Pro	Rodinal	1+50	125	16	16	16	20C	
Delta 3200 Pro	Rodinal	1+25	400	5.5	5.5		20C	
Delta 3200 Pro	Rodinal	1+25	800	7	7		20C	
Delta 3200 Pro	Rodinal	1+25	1000	8.5			20C	
Delta 3200 Pro	Rodinal	1+25	1600	9	9		20C	
Delta 3200 Pro	Rodinal	1+63	1600	28			20C	
Delta 3200 Pro	Rodinal	1+25	3200	11	11		20C	
Delta 3200 Pro	Rodinal	1+25	6400	20	20		20C	
Delta 400 Pro	Rodinal	1+50	200	11	11		20C	
Delta 400 Pro	Rodinal	1+25	200	6.5	6.5		20C	
Delta 400 Pro	Rodinal	1+24	250	7.5			20C	
Delta 400 Pro	Rodinal	1+25	400	9	9		20C	
Delta 400 Pro	Rodinal	1+50	400	20	20		20C	
Delta 400 Pro	Rodinal	1+100	400	36			20C	[35c]
Delta 400 Pro	Rodinal	1+200	400		105		20C	[52]
Delta 400 Pro	Rodinal	1+25	800	16	16		24C	
Delta 400 Pro	Rodinal	1+25	800	18.5			20C	
Delta 400 Pro	Rodinal	1+16	1600		20		20C	
Earl Grey	Rodinal	1+25	100	4			20C	
Earl Grey	Rodinal	1+50	100	8			20C	
Eastman Double-X (5222)	Rodinal	1+25		5.75			20C	

Eastman Double-X (5222)	Rodinal	1+100	25	3			20C	
Eastman Double-X (5222)	Rodinal	1+60	200	7			20C	
Eastman Double-X (5222)	Rodinal	1+20	200	5			20C	
Eastman Double-X (5222)	Rodinal	1+50	250	11			20C	
Eastman Double-X (5222)	Rodinal	1+50	400	11			20C	
Eastman Double-X (5222)	Rodinal	1+20	1600	10			20C	
Eastman Double-X (5222)	Rodinal	1+300	6400	8 hrs			20C	
Efke 100	Rodinal	1+50	50	9	9		20C	
Efke 100	Rodinal	1+25	80	5			20C	
Efke 100	Rodinal	1+50	100	10	10	10	20C	
Efke 100	Rodinal	1+75	100		13.5		20C	
Efke 100	Rodinal	1+100	100	16	16	16	20C	
Efke 100	Rodinal	1+25	100	6	6	6	20C	
Efke 100	Rodinal	1+25	160		8		20C	
Efke 100	Rodinal	1+50	200	14	14	14	20C	
Efke 100	Rodinal	1+25	400		13.5		20C	
Efke 100	Rodinal	1+75	400	19.5	19.5		20C	[ss]
Efke 100	Rodinal	1+50	400	24	24	24	20C	
Efke 25	Rodinal	1+50	12	3.5			20C	
Efke 25	Rodinal	1+100	12	9	9		20C	
Efke 25	Rodinal	1+99	20	6.5	6.5		20C	
Efke 25	Rodinal	1+50	20	4	4		20C	
Efke 25	Rodinal	1+100	25	10			24C	[37][48][r]
Efke 25	Rodinal	1+100	25	17	18		21C	
Efke 25	Rodinal	1+25	25	4	4		20C	
Efke 25	Rodinal	1+50	25	8	8		20C	
Efke 25	Rodinal	1+100	25	12			20C	
Efke 25	Rodinal	1+100	25		11		20C	[25a]
Efke 50	Rodinal	1+50	50	9	9		20C	
Efke 50	Rodinal	1+25	50	6	6		20C	
Efke 50	Rodinal	1+100	50	18	18		20C	
Efke IR820	Rodinal	1+25	n/a	9	9	9	20C	
Efke IR820	Rodinal	1+50	1.5			14	20C	[5]
Efke IR820	Rodinal	1+50	3		11		20C	[5]
Efke IR820	Rodinal	1+50	4		11		20C	[5]
Ektagaphic HC	Rodinal	1+100	6	18			20C	[gt][15]
Ektapan	Rodinal	1+50	100			13	21C	
ERA 100	Rodinal	1+50	100	14			20C	
ERA PSS 45 Pan	Rodinal	1+100	100			60	20C	[52]
Fomapan 100	Rodinal	1+100	50	7			20C	[17]
Fomapan 100	Rodinal	1+25	100			6.5	20C	[21][40][ss]
Fomapan 100	Rodinal	1+200	100	30			20C	[35b]
Fomapan 100	Rodinal	1+25	100	4	4	3.5	20C	
Fomapan 100	Rodinal	1+37	100		6.25		20C	
Fomapan 100	Rodinal	1+19	100			6.5	20C	
Fomapan 100	Rodinal	1+50	100	8-9	8-9	8-9	20C	
Fomapan 100	Rodinal	1+100	100			10	20C	
Fomapan 100	Rodinal	1+50	200		21.5		20C	
Fomapan 100	Rodinal	1+100	400		26		20C	
Fomapan 200	Rodinal	1+25	200	5			20C	
Fomapan 200	Rodinal	1+50	200	8			20C	
Fomapan 200	Rodinal	1+50	200	10			20C	
Fomapan 200	Rodinal	1+50	400		14		20C	
Fomapan 400	Rodinal	1+50	200	11			20C	
Fomapan 400	Rodinal	1+25	400	5.5			20C	
Fomapan 400	Rodinal	1+50	400	11			20C	
Fomapan 400	Rodinal	1+50	800		19		20C	
Fomapan 400	Rodinal	1+50	1600	24			20C	
Fomapan 400	Rodinal	1+25	3200		25		20C	[15][cc]
Fomapan T800	Rodinal	1+50	800	13			20C	
Fortepan 100	Rodinal	1+25	100	5	5		20C	
Fortepan 100	Rodinal	1+50	100	9	9		20C	
Fortepan 100	Rodinal	1+50	200	15			20C	

Fortepan 200	Rodinal	1+25		7.5			20C	
Fortepan 200	Rodinal	1+50	200		13		20C	
Fortepan 200	Rodinal	1+50	200	11			20C	
Fortepan 200	Rodinal	1+50	200	9			24C	
Fortepan 200	Rodinal	1+50	200	10	10	10	20C	
Fortepan 200	Rodinal	1+25	200	5			24C	
Fortepan 400	Rodinal	1+50	400	12	12	12	20C	
Fortepan 400	Rodinal	1+25	400	7.5	7.5	7.5	20C	
Fortepan 400	Rodinal	1+25	800	10	10	10	20C	
Fortepan Portrait	Rodinal	1+50	100		9		20C	
FP4+	Rodinal	1+25	25	4	4		20C	[s]
FP4+	Rodinal	1+100	64	21			20C	
FP4+	Rodinal	1+24	80	7.5			20C	
FP4+	Rodinal	1+50	100	12			20C	
FP4+	Rodinal	1+50	125	15	15	15	20C	
FP4+	Rodinal	1+100	125	20	20	20	20C	[17]
FP4+	Rodinal	1+25	125	9	9	9	20C	
FP4+	Rodinal	1+25	200	13	13	13	20C	
FP4+	Rodinal	1+50	200	20	20	20	20C	
FP4+	Rodinal	1+50	250	26			20C	
FP4+	Rodinal	1+24	400	20			20C	
Fuji HRT Green Full Speed	Rodinal	1+50	400			11	20C	
Fuji HRT Green Full Speed	Rodinal	1+100	400			37	20C	[35c]
HIE Infrared	Rodinal	1+50	n/a	12		12	20C	
HIE Infrared	Rodinal	1+25	n/a	9		9	20C	
HIE Infrared	Rodinal	1+50	400	12			20C	
HIE Infrared	Rodinal	1+50	1600	20			20C	[11]
HP5+	Rodinal	1+50	25	7			20C	
HP5+	Rodinal	1+50	100	9			20C	
HP5+	Rodinal	1+100	160	20	20	20	20C	[17]
HP5+	Rodinal	1+50	200	10	10		20C	
HP5+	Rodinal	1+25	200		4.75		20C	[1]
HP5+	Rodinal	1+75	200	17			20C	
HP5+	Rodinal	1+50	200	13			20C	
HP5+	Rodinal	1+36	200		7.5		20C	[s]
HP5+	Rodinal	1+25	200	5			20C	
HP5+	Rodinal	1+50	250			12	24C	
HP5+	Rodinal	1+25	320	15	15		20C	
HP5+	Rodinal	1+25	400	6	6	6	20C	
HP5+	Rodinal	1+50	400	11	11	11	20C	
HP5+	Rodinal	1+50	400	7.25			24C	[1][26]
HP5+	Rodinal	1+100	400	16			20C	
HP5+	Rodinal	23+1000	400	13.5			20C	
HP5+	Rodinal	1+100	400	80			21C	[35a]
HP5+	Rodinal	1+25	800	8	8	8	20C	
HP5+	Rodinal	1+50	800	16	16	16	20C	
HP5+	Rodinal	1+100	1600	90			20C	
HP5+	Rodinal	1+200	1600	240			20C	[52]
HP5+	Rodinal	1+50	1600	24	24	24	20C	
HP5+	Rodinal	1+25	1600	12	12	12	20C	
HP5+	Rodinal	1+100	1600		120		20C	[52]
HP5+	Rodinal	1+25	3200	18			21C	
Ilford Pan 100	Rodinal	1+50	100	15			20C	
Ilford Pan 100	Rodinal	1+25	100	9			20C	
Ilford Pan 100	Rodinal	1+25	200	13			20C	
Ilford Pan 100	Rodinal	1+50	200	20			20C	
Ilford Pan 400	Rodinal	1+50	200	9			20C	
Ilford Pan 400	Rodinal	1+25	200	5			20C	
Ilford Pan 400	Rodinal	1+100	400		35		20C	
Ilford Pan 400	Rodinal	1+25	400	6			20C	
Ilford Pan 400	Rodinal	1+100	400	120			20C	[52]
Ilford Pan 400	Rodinal	1+50	400	11			20C	
Ilford Pan 400	Rodinal	1+25	800	8			20C	

IR 750	Rodinal	1+50	n/a	5	5		20C	
IR 750	Rodinal	1+75	n/a	9	9		20C	
IR 750	Rodinal	1+100	6		4.5		20C	[4]
JandC Pro 100	Rodinal	1+100	100	21			20C	
JandC Pro 100	Rodinal	1+50	100	13.5			20C	
JandC Pro 100	Rodinal	1+25	100	8.5			20C	
Jessop Pan 100s	Rodinal	1+25	100	8			20C	
Jessop Pan 400s	Rodinal	1+25	400	7			20C	
Jessop Pan 400SX	Rodinal	1+25	400	10			20C	
Kentmere 100	Rodinal	1+50	50	9			20C	
Kentmere 400	Rodinal	1+50	400	20			20C	
Kentmere 400	Rodinal	1+25	400	7.5			20C	
Lady Grey	Rodinal	1+50	400	10			20C	
Lady Grey	Rodinal	1+25	400	5			20C	
Legacy Pro 100	Rodinal	1+50	80	11.5			20C	
Legacy Pro 100	Rodinal	1+50	100	13.5			20C	
Legacy Pro 100	Rodinal	1+25	100	7			20C	
Legacy Pro 400	Rodinal	1+50	200-250	8-9			20C	
Legacy Pro 400	Rodinal	1+100	200	15			20C	
Legacy Pro 400	Rodinal	1+100	250	20			20C	
Legacy Pro 400	Rodinal	1+25	250	4.5			20C	
Legacy Pro 400	Rodinal	1+50	400	11			20C	
Legacy Pro 400	Rodinal	1+25	400	6			20C	
Legacy Pro 400	Rodinal	1+25	1600	10			20C	
Maco CUBE400c	Rodinal	1+25	400	12	12		20C	
Maco Eagle AQS	Rodinal	1+25	400	12-15			20C	
Maco IR 820c/750c	Rodinal	1+25	n/a	9	9	9	20C	
Maco IR 820c/750c	Rodinal	1+50	4		11		20C	[5]
Maco ORT25c	Rodinal	1+100	12	10	10		20C	[13]
Maco ORT25c	Rodinal	1+10	25	5	5	5	20C	[15]
Maco ORT25c	Rodinal	1+25	25	4	4	4	20C	[13]
Maco ORT25c	Rodinal	1+25	25	7	7	7	20C	[28]
Maco UP100p/PO100c	Rodinal	1+25	100	8	6-8	8	20C	
Maco UP25P	Rodinal	1+25	25	7	7		20C	
Maco UP400p	Rodinal	1+25	400	10	10		20C	
Maco UP64c	Rodinal	1+25	64	7	7		20C	
Neopan 100 Acros	Rodinal	1+50	50		11		20C	
Neopan 100 Acros	Rodinal	1+50	64		10		20C	[1]
Neopan 100 Acros	Rodinal	1+50	80	11.5			20C	
Neopan 100 Acros	Rodinal	1+50	100		8		24C	
Neopan 100 Acros	Rodinal	1+100	100		18		20C	[q]
Neopan 100 Acros	Rodinal	1+50	100		13.5		20C	[cb]
Neopan 100 Acros	Rodinal	1+25	125		6.75		20C	
Neopan 100 Acros	Rodinal	1+25	200		14		20C	
Neopan 100 Acros	Rodinal	1+25	400		7.75			[mm]
Neopan 100ss	Rodinal	1+25	100	7-10	7-10		20C	
Neopan 100ss	Rodinal	1+50	100	14-16	14-16		20C	
Neopan 1600	Rodinal	1+25	200	3			20C	
Neopan 1600	Rodinal	1+100	250	15			20C	
Neopan 1600	Rodinal	1+49	320	5			20C	
Neopan 1600	Rodinal	1+100	400	20			20C	[15]
Neopan 1600	Rodinal	1+25	400	3.5			20C	
Neopan 1600	Rodinal	1+25	1600	5			20C	
Neopan 1600	Rodinal	1+50	1600	8			20C	
Neopan 1600	Rodinal	1+25	3200	7.5			20C	
Neopan 400	Rodinal	1+50	200-250	8-9	8-9		20C	
Neopan 400	Rodinal	1+100	200	15	15		20C	
Neopan 400	Rodinal	1+100	250	20	20		20C	
Neopan 400	Rodinal	1+25	250	4.5	4.5		20C	
Neopan 400	Rodinal	1+100	250	13			24C	
Neopan 400	Rodinal	1+50	400	11	11		20C	
Neopan 400	Rodinal	1+25	400	6	6		20C	
Neopan 400	Rodinal	1+25	800	7.5			22C	

Neopan 400	Rodinal	1+25	1600	10			20C	
Orca 110	Rodinal	1+50	100	9			20C	
Orca 110	Rodinal	1+100	100	25			20C	
Ortho Plus	Rodinal	1+100	40			10	20C	[13]
Orwo N74	Rodinal	1+50	400	13			20C	
Orwo UN54	Rodinal	1+100	100	25			20C	[35a]
Orwo UN54	Rodinal	1+50	100	8-10			20C	
Pan 400	Rodinal	1+50	400	23			20C	
Pan F+	Rodinal	1+100	25	15	15		20C	
Pan F+	Rodinal	1+24	40	5			20C	
Pan F+	Rodinal	1+50	50	11	11		20C	
Pan F+	Rodinal	1+100	50		60		20C	[35c]
Pan F+	Rodinal	1+80	50	17			20C	
Pan F+	Rodinal	1+19	50		5		20C	
Pan F+	Rodinal	1+25	50	6	6		20C	
Pan F+	Rodinal	1+50	64	12	12		20C	
Pan F+	Rodinal	1+50	80	13.5			20C	
Phototec 400	Rodinal	1+25	800	9			24C	
Plus-X	Rodinal	1+100	64	10			20C	
Plus-X	Rodinal	1+25	125	6	6	6	20C	[29]
Plus-X	Rodinal	1+50	125	13	13	13	20C	[29]
Plus-X	Rodinal	1+85	200	12	12	12	24C	[29]
Polypan F	Rodinal	1+50	25	8.5			20C	[n]
Polypan F	Rodinal	1+100	50	60			20C	[56][52]
Polypan F	Rodinal	1+100	50	40			20C	[35b]
Polypan F	Rodinal	1+49	50	7-8			20C	
Polypan F	Rodinal	1+25	50	6			20C	
Polypan F	Rodinal	1+100	100	60			20C	[35a]
Polypan F	Rodinal	1+90	100	60			20C	[35a]
Polypan F	Rodinal	1+100	100	65			20C	[35b]
Polypan F	Rodinal	1+50	100	17			20C	
Recording Film	Rodinal	1+50	640-1000	10			20C	
Recording Film	Rodinal	1+25	640-1000	4.5			20C	
Retro 100 Tonal	Rodinal	1+50	100	13	13	13	20C	
Rollei ATO 2.1	Rodinal	1+300	1	12	12		20C	
Rollei ATP 1.1	Rodinal	1+150	15	6.5			20C	
Rollei ATP 1.1	Rodinal	1+300	20		12		20C	
Rollei ATP 1.1	Rodinal	1+300	25	12			20C	
Rollei Infrared	Rodinal	1+50	400 (25)	12	12	12	20C	[56][57]
Rollei Infrared	Rodinal	1+25	400 (10-25)	7.5	7.5	7.5	20C	[56][57]
Rollei Infrared	Rodinal	1+100	400 (10-25)	21.5			21C	
Rollei Ortho 25	Rodinal	1+25	25	4	4	4	20C	
Rollei Ortho 25	Rodinal	1+50	25	10			21C	
Rollei Ortho 25	Rodinal	1+50	25	6	6	6	20C	
Rollei Pan 25	Rodinal	1+50	25	11	11	11	20C	
Rollei Pan 25	Rodinal	1+100	25	20			20C	[25b]
Rollei Pan 25	Rodinal	1+25	25	6	6	6	20C	
Rollei R3	Rodinal	1+25	400		12		20C	
Rollei R3	Rodinal	1+25	400		12		20C	
Rollei Retro 100	Rodinal	1+50	50	11.5			20C	[30]
Rollei Retro 100	Rodinal	1+24	64	7.5			20C	[30]
Rollei Retro 100	Rodinal	1+50	80		12		20C	
Rollei Retro 100	Rodinal	1+50	100		13		20C	[26][30]
Rollei Retro 100	Rodinal	1+50	100	13			20C	
Rollei Retro 100	Rodinal	1+25	125	8	8	8	20C	
Rollei Retro 100	Rodinal	1+50	160	17	17	17	20C	
Rollei Retro 100	Rodinal	1+25	160	9.5			20C	
Rollei Retro 100	Rodinal	1+50	200	21.5			20C	
Rollei Retro 100	Rodinal	1+25	200	11	11	11	20C	[30]
Rollei Retro 100	Rodinal	1+25	400	15			20C	
Rollei Retro 100	Rodinal	1+50	400	29			20C	
Rollei Retro 400	Rodinal	1+50	200	10			20C	
Rollei Retro 400	Rodinal	1+100	200	15	15		20C	[17][30]

Rollei Retro 400	Rodinal	1+24	250	5			20C	[30]
Rollei Retro 400	Rodinal	1+49	250	8			20C	[30]
Rollei Retro 400	Rodinal	1+25	320	10	10		20C	
Rollei Retro 400	Rodinal	1+50	320-500	11	11		20C	[30]
Rollei Retro 400	Rodinal	1+50	320	30	30		20C	
Rollei Retro 400	Rodinal	1+25	320-400	7	7		20C	[30]
Rollei Retro 400	Rodinal	1+100	400	17			24C	[a][30]
Rollei Retro 400	Rodinal	1+100	400	22			24C	[a][30]
Rollei Retro 400	Rodinal	1+25	800	14			20C	
Rollei Retro 400S	Rodinal	1+50	400	22	22		20C	
Rollei Retro 400S	Rodinal	1+25	400	10.5	10.5		20C	
Rollei Retro 400S	Rodinal	1+100	400		60		20C	[35a]
Rollei Retro 400S	Rodinal	1+100	400	20			22C	
Rollei Retro 80S	Rodinal	1+50	40	10	10		20C	
Rollei Retro 80S	Rodinal	1+100	64	40			20C	[35a]
Rollei Retro 80S	Rodinal	1+50	80	14	14		20C	
Rollei Retro 80S	Rodinal	1+100	80		60		20C	[17][35b]
Rollei Retro 80S	Rodinal	1+200	80	65			20C	[52]
Rollei Retro 80S	Rodinal	1+200	100	110			20C	[35b]
Rollei RPX 100	Rodinal	1+25	50	7	7		20C	
Rollei RPX 100	Rodinal	1+25	100	9	9		20C	
Rollei RPX 100	Rodinal	1+50	100	18	17		20C	
Rollei RPX 100	Rodinal	1+50	200	20.5	20.5		20C	
Rollei RPX 100	Rodinal	1+25	200	13	13		20C	
Rollei RPX 400	Rodinal	1+25	400	8	8		20C	
Rollei RPX 400	Rodinal	1+50	800	10			22C	
Rollei Superpan 200	Rodinal	1+100	125	24			20C	
Rollei Superpan 200	Rodinal	1+100	200	45			20C	
Rollei Superpan 200	Rodinal	1+25	200	8	8		20C	
Rollei Superpan 200	Rodinal	1+50	200	17	17		20C	
SFX 200	Rodinal	1+50	200	10	10		20C	
SFX 200	Rodinal	1+25	200	6	6		20C	
SFX 200	Rodinal	1+49	200		15		20C	[47]
Shanghai GP3 Pan 100	Rodinal	1+25	50		6		20C	
Shanghai GP3 Pan 100	Rodinal	1+200	100			120		[35a]
Shanghai GP3 Pan 100	Rodinal	1+50	100		15	15	20C	
Shanghai GP3 Pan 100	Rodinal	1+25	100		10		20C	
Shanghai GP3 Pan 100	Rodinal	1+100	100			60	20C	[52]
Shanghai GP3 Pan 100	Rodinal	1+25	400			35	20C	
Shanghai GP3 Pan 100	Rodinal	1+100	400		120		20C	[35a]
SHD 100	Rodinal	1+25	100	6.5			20C	[n]
SHD 100	Rodinal	1+50	100		12		20C	
SHD 100	Rodinal	1+100	100	20-24			20C	[b]
SHD 100	Rodinal	1+25	100		7		20C	
SHD 100	Rodinal	1+200	100		120		20C	[52]
SHD 100	Rodinal	1+25	200	9.5			20C	
SHD 400	Rodinal	1+50	400	14-16			20C	
SHD 400	Rodinal	1+25	400		7		20C	
Surveillance P3	Rodinal	1+50	400	14			20C	
Svema 200 Reporter	Rodinal	1+25	200	5			18C	
Svema A2-SH	Rodinal	1+50	400	20			20C	
Svema FN64	Rodinal	1+50	64-125	11			20C	
Svema FN64	Rodinal	1+25	64	6.25			20C	
Svema FN64	Rodinal	1+50	64	10.5			20C	
Svema ZT-8	Rodinal	1+50	100	11			20C	[15][52]
SvemaFoto 250	Rodinal	1+25	100		8.5		20C	
SvemaFoto 32	Rodinal	1+50	32	12			20C	
Tasma 100 Super	Rodinal	1+50	100	9			20C	
Tasma FN-64	Rodinal	1+50	64	12			20C	
Tasma KN-1	Rodinal	1+50	100	22			20C	
Technical Pan	Rodinal	1+99	16	4			20C	[13]
Technical Pan	Rodinal	1+125	20	8			20C	
Technical Pan	Rodinal	1+300	25	30			20C	[13] [25]



Technical Pan	Rodinal	1+100	25	8			21C	<a href="#">[gz]</a>
Technical Pan	Rodinal	1+100	25		60		20C	<a href="#">[35a]</a>
Technical Pan	Rodinal	1+150	25-64	7	7	7	20C	<a href="#">[13]</a>
Technical Pan	Rodinal	1+300	25-64	12	12	12	20C	<a href="#">[13]</a>
Technical Pan	Rodinal	1+50	25	4.5	4.5	4.5	20C	<a href="#">[14]</a>
Technical Pan	Rodinal	1+100	25	7-9	7-9	7-9	20C	<a href="#">[14]</a>
Technical Pan	Rodinal	1+100	25	8			21C	<a href="#">[k]</a>
TMax 100	Rodinal	1+50	50	10			20C	
TMax 100	Rodinal	1+75	50	17	17		20C	<a href="#">[29]</a>
TMax 100	Rodinal	1+25	64-100	5.5-6	5.5	5.5	20C	<a href="#">[29]</a>
TMax 100	Rodinal	1+100	64	15	15	15	20C	<a href="#">[29]</a>
TMax 100	Rodinal	1+50	80-100	12	12	12	20C	
TMax 100	Rodinal	1+100	80	20	20	20	20C	<a href="#">[29]</a>
TMax 100	Rodinal	1+75	100		19		20C	
TMax 100	Rodinal	1+100	100	60			20C	<a href="#">[52]</a>
TMax 400	Rodinal	1+50	100	3.75			20C	
TMax 400	Rodinal	1+100	160	20	20	20	20C	
TMax 400	Rodinal	1+100	200	60			20C	<a href="#">[52]</a>
TMax 400	Rodinal	1+50	200	8	8		20C	
TMax 400	Rodinal	1+50	250	8.5			20C	
TMax 400	Rodinal	1+24	320	5			20C	
TMax 400	Rodinal	1+49	320	9			20C	
TMax 400	Rodinal	1+25	400	5	5	5	20C	
TMax 400	Rodinal	1+80	400	16			21C	
TMax 400	Rodinal	1+50	400	10	10	10	20C	
TMax 400	Rodinal	1+100	400	120			18C	<a href="#">[35a]</a>
TMax 400	Rodinal	1+300	640	150			21C	<a href="#">[52]</a>
TMax 400	Rodinal	1+100	800		24		20C	<a href="#">[k]</a>
TMax 400	Rodinal	1+25	1600	11	11		20C	
TMax P3200	Rodinal	1+24	1000	7			20C	<a href="#">[29]</a>
TMax P3200	Rodinal	1+25	1250-3200	8			20C	<a href="#">[29]</a>
TMax P3200	Rodinal	1+50	1250-3200	16			20C	<a href="#">[29]</a>
TMax P3200	Rodinal	1+25	6400	10.5			20C	<a href="#">[29]</a>
Tri-X 320	Rodinal	1+25	200			7	20C	<a href="#">[1]</a>
Tri-X 320	Rodinal	1+50	320		15		20C	
Tri-X 320	Rodinal	1+100	320		20		20C	
Tri-X 320	Rodinal	1+50	320			14	21C	<a href="#">[21]</a>
Tri-X 400	Rodinal	1+50	100	7.5			20C	
Tri-X 400	Rodinal	1+50	200	9			20C	
Tri-X 400	Rodinal	1+25	200		7		20C	
Tri-X 400	Rodinal	1+100	250	15	15		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+100	250	20			20C	<a href="#">[gz]</a>
Tri-X 400	Rodinal	1+50	320	9.5			20C	<a href="#">[1]</a>
Tri-X 400	Rodinal	1+24	320	6			20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+35	400	10			20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+100	400	20	20		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+75	400	17.5	17.5		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+60	400	15	15		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+50	400	13	13		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+25	400	7	7		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+100	400	24			21C	<a href="#">[m]</a>
Tri-X 400	Rodinal	1+50	640	15.5			20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+50	800	13			23C	
Tri-X 400	Rodinal	1+100	800	17.5	17.5		24C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+50	800	16.5	16.5		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+50	1600	18.5	18.5		20C	<a href="#">[29]</a>
Tri-X 400	Rodinal	1+50	3200	33			20C	<a href="#">[r]</a>
Tri-X 400	Rodinal	1+50	3200	33			20C	<a href="#">[r]</a>
Tri-X 400	Rodinal	1+50	12800	51			20C	<a href="#">[35c]</a>
Tura P100	Rodinal	1+25	100	8			20C	
Tura P100	Rodinal	1+50	100	17			20C	
Tura P400	Rodinal	1+50	400	11			20C	
Tura P400	Rodinal	1+25	400	7			20C	

Ultrafine Plus 100	Rodinal	1+100	100	14			20C	
Ultrafine Plus 100	Rodinal	1+100	200	18			20C	
Universal 100	Rodinal	1+25	100	5.5			20C	
Universal 100	Rodinal	1+25	200	8.5			20C	
Verichrome Pan	Rodinal	1+50	64		10		20C	
XP2	Rodinal	1+100	200-800	120			20C	<a href="#">[52]</a> <a href="#">[54]</a>
XP2	Rodinal	1+25	400	18			20C	<a href="#">[54]</a>

The Massive Dev Chart  
<http://www.digitaltruth.com>

© Digitaltruth Photo Ltd, All Rights Reserved.